



# Replay 33K

Technical Data Sheet



Revised 23/10/2024

# CHARACTERISTICS OF THE MATERIAL

## STEREO MICROSCOPIC OBSERVATION

The figure below shows the product and the stereo microscopic observation of the cutting surface of the **Replay 33K**.




## DSC ANALYSIS

The **Replay 33K** material was analyzed by DSC with the following thermal program:

- 1° heating from -10°C a 280°C, 20 °C/min in N<sub>2</sub>
- Cooling from 280°C a -10°C, -20 °C/min in N<sub>2</sub>
- 2° heating from -10°C a 280°C, 20 °C/min in N<sub>2</sub>

The figure below shows the DSC thermogram relating to the **Replay 33K** samples



*Replay 33K thermogram*

The DSC analysis shows that the **Replay 33K** granule is composed by of three main polymers, such as LDPE, HDPE and PP as demonstrated by the three different melting points in the thermogram. The table shows the indicative percentages calculated based on the fusion enthalpy.

<b>Replay 33K</b>	
	<b>% in the blend (*)</b>
<b>LLDPE/LDPE</b>	25
<b>HDPE</b>	25
<b>PP</b>	> 45

*Composition of Replay 33K (\*) The reported components percentages are indicative*

### **MELT FLOW RATE (MFR)**

A MFR analysis was carried out on **Replay 33K** granules according to the ASTM D1238A standard with a weight of 2.16 kg. The analysis was performed at **190 °C**, preheating the sample for 180 seconds and recovering the material for 60 seconds. The average result of MFR is reported in the table below.

<b>Sample</b>	<b>MFR (Average data)</b>
Replay 33K	<b>8 g/10 min</b>

*Average result of MFR*

### **MOISTURE ASSESSMENT**

The moisture assessment was performed following the UNI 10667-16 standard. A **Replay 33K** sample was dried into an oven at 100°C for 8 h. The residual moisture in the granules was less/equal to 0.2%

<b>Sample</b>	<b>% Moisture (Average data)</b>
Replay 33K	≤ 0.2

*Average values of moisture in the Replay 33K granules*

## ASH ANALYSIS


The ashes were analyzed in accordance with the ISO 3451 and they were analyzed also by FT-IR spectroscopy. The analysis shows the presence of **inorganic salts, silicates and calcium oxide**. The table shows the results of the quantitative analysis carried out on the **Replay 33K**.

Sample	% ashes (Average data)
Replay 33K	1.9

*Average result for ashes determination*

## DMA ANALYSIS

The sample of **Replay 33K** was analyzed by DMA in single cantilever mode with an oscillation frequency equal to 1Hz, according in a range of temperature between a thermal program -40 °C to 100 °C at 5 °C/ min.



*DMA graph of Replay 33K, the red curve indicates the storage modulus E' blue curve the TanDelta*

The **Replay 33K** has an initial storage modulus E' equal to 4,36E+08 Pa and a storage modulus E' at 25 °C equal to 2.43+08 Pa. The glass transition temperature is not visible in the analyzed temperature range.

## TECHNICAL DATA SHEET

### Replay 33K – Polyolefin blends

Property	Test method	Test conditions	Unit of measurement	Typical value
<b>PHYSICAL</b>				
Density	ASTM D 792-91	23°C	g/cm <sup>3</sup>	0,923
Melt Flow Rate (MFR)	ASTM D 1238A	190/2,16	g/10 min	8.0
Ash percentage	ISO 3451		%	1.9
Moisture percentage	UNI 10667-16		%	≤ 0.2
<b>MECHANICAL</b>				
Izod impact strength test	ISO 180A	23°C	KJ/m <sup>2</sup>	43 ±6
Izod impact strength test	ISO 180A	-20°C	KJ/m <sup>2</sup>	22 ±3
Bending modulus of elasticity	ISO 178		N/mm <sup>2</sup>	888
Tensile strength modulus of elasticity	ISO 527		N/mm <sup>2</sup>	984
<b>THERMAL</b>				
HDT Heat Deflection Temperature	ASTM D 648-96		°C	nd
VICAT Heat penetration index	ASTM D 1525-96		°C	nd
Melting point (for each mixture peak)	ASTM D 3418-97		°C	118,127,162
<b>MOLDING CONDITIONS</b>				
Barrel temperature			°C	190-220
Mould temperature			°C	30-60
Drying temperature			°C	60-80
Drying time			h	4
<p>The product complies with the UNI 10667 standard</p> <p>The data shown are the average values of a significant sample of the product and are provided to supply information to the user; they do not constitute any warranty and do not imply in general terms any guarantee or commitment by the Company. The mean value obtained in the tensile tests have a confidence interval established at 95% of the mean value.</p>				

## COMPLIANCE OF THE MATERIAL WITH THE REACH REGULATION

The table shows the results of the analysis performed on the sample to assess its compliance with the Reach Regulation.

Parameter	Unit of measurement	Method	Result
PCB (polychlorinated biphenyl)	mg/kg	EPA 3550C EPA8270E	< 310

CHLOROPARAFFINS		EPA 3550C EPA8270E	
C10-C13	mg/kg		< 10
C14-C17	mg/kg		< 10
C18-C20	mg/kg		< 10

PHTHALATES		EN ISO 16181-1:2021	
DI-N-BUTYL PHTHALATE (DBP)	mg/kg		<50
DI - ISOBUTYL PHTHALATE (DIBP)	mg/kg		<50
BENZYL BUTYL PHTHALATE (BBP)	mg/kg		<50
BIS(2-ETHYLHEXYL) PHTHALATE (DEHP)	mg/kg		72
DI-ISO NONYL PHTHALATE (DINP)	mg/kg		<50
DI-ISO DECIL PHTHALATE (DINP)	mg/kg		<50
DI-N -OCTIL PHTHALATE (DNOP)	mg/kg		<50

POLYCYCLIC AROMATIC HYDROCARBONS (IPA)		EPA 3550C EPA8270E	
NAPHTHALENE	µg/kg		<100
ACENAPHTHYLENE	µg/kg		<100
ACENAPHTHENE	µg/kg		<100
FLUORENE	µg/kg		<100
PHENANTHRENE	µg/kg		<100
ANTHRACENE	µg/kg		<100
FLUORANTHENE	µg/kg		<100
PYRENE	µg/kg		<100
BENZ(a)ANTHRACENE	µg/kg		<100
CHRYSENE	µg/kg		<100
BENZO(b)FLUORANTHENE	µg/kg		<100
BENZO(k)FLUORANTHENE	µg/kg		<100
BENZO(j)FLUORANTHENE	µg/kg		<100
BENZO(e)PYRENE	µg/kg		<100
BENZO(a)PYRENE	µg/kg		<100
PERYLENE	µg/kg		<100
INDENO(1,2,3-cd)PYRENE	µg/kg		<100
DIBENZ(a,h)ANTHRACENE	µg/kg		<100
BENZO(g,h,i)PERYLENE	µg/kg		<100
DIBENZO(a,l)PYRENE	µg/kg		<100
DIBENZO(a,e)PYRENE	µg/kg		<100
DIBENZO(a,i)PYRENE	µg/kg		<100
DIBENZO(a,h)PYRENE	µg/kg		<100

HEXAVALENT CHROMIUM (CR VI)	mg/kg	ION CHROMATOGRAPHY	<1.0
<b>HEAVY METALS</b>			
ANTIMONY	mg/kg	UNI EN 13657 UNI EN ISO11885	<9,1
ARSENIC	mg/kg	UNI EN 13657 UNI EN ISO11885	<21,3
CADMIUM	mg/kg	UNI EN 13657 UNI EN ISO11885	<5,0
CHROMIUM	mg/kg	UNI EN 13657 UNI EN ISO11885	6,3
MERCURY	mg/kg	UNI EN 13657 EPA 6010C	<2,8
NICKEL	mg/kg	UNI EN 13657 UNI EN ISO11885	<7,0
LEAD	mg/kg	UNI EN 13657 UNI EN ISO11885	20,7
COPPER	mg/kg	UNI EN 13657 UNI EN ISO11885	19,9
SELENIUM	mg/kg	UNI EN 13657 UNI EN ISO11885	<62,9
TIN	mg/kg	UNI EN 13657 UNI EN ISO11885	<10,5
TELLURIUM	mg/kg	UNI EN 13657 UNI EN ISO11885	<26,0
ZINC	mg/kg	UNI EN 13657 UNI EN ISO11885	88,8

## APPLICATION EXAMPLES AND CURRENT PROJECTS





## REVET SPA

Società soggetta a Direzione e Coordinamento da parte di Alia servizi ambientali Spa Viale America,  
104 • Loc. Gello • 56025 • Pontedera (PI)  
Tel. 0587 271211 • Fax 0587 271269  
info@revet.

[www.revet.com](http://www.revet.com)



EuCertPlast